


Wall fastening



! Note !
 The owner has to bevel the wall edges in the bend areas min. 50x50 mm from step edge vertical up to 1800 mm height !

concrete or stone wall min. 200 mm thick

NOTE !
 You have to assign 40 mm more for a HIRO 370 platform for each stair-flight-side as by HIRO 320-platform sizes !

- 1225 (800x1000)
- 1145 (750x840)
- 1080 (680x840)
- 1065 (680x750)
- 1010 (620x750)–Special
- 1120 (680x750)–HIRO 361

				HIRO 320-360-370		Scale: 1 : 10
				Min. Staircase Measurement for Wall Fastening		Weight:
		Date	Name	HIRO LIFT Bielefeld		Page 1
		23.11.2005	Beckmann			
		Approval			Business-Nr.: Interior order	Page 1
		Drawing-Nr.:	Platform 2/G2			
Position	Changing	Date	Name	Construction Nr.:		